C-LN

Base Product



Fiber Optic Cable, Indoor/outdoor Low Smoke Zero Halogen, CPR-only flame rated, Stranded Loose Tube All-Dielectric

- Indoor/outdoor cables are tough enough for outdoor use while also being listed for indoor use
- Superior mechanical and optical performance with unmatched stability and quality
- Available Jacket Colors: Aqua, Black and Yellow

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-LN

Ordering Note Available cable jacket colors: aqua,black, yellow


General Specifications

Cable Type Stranded loose tube

Construction Type All Dielectric | Non-armored

C-LN

Ordering Tree



Environmental Specifications

Installation temperature-30 °C to +60 °C (-22 °F to +140 °F)Operating Temperature-40 °C to +70 °C (-40 °F to +158 °F)Storage Temperature-40 °C to +75 °C (-40 °F to +167 °F)Environmental SpaceLow Smoke Zero Halogen (LSZH)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

