
# BLK-RCT-A02D0



Fiber Optic Ribbon Breakout Kit, 1-12F/ribbon, 240-432F/tube, 11-15 mm central tube outside dia., 2 tubes/leg

#### **Product Classification**

Regional Availability Latin America | North America

**Product Type** Fiber breakout kit, round

Product Series BLK-R

## General Specifications

**Application** For use with ribbon fiber cables

Breakout Legs, quantity 1

Fibers per Ribbon, maximum 12

Fibers per Tube, maximum 672

**Tube Type** Ribbon central tube

Tubes per Leg, quantity 2

**Dimensions** 

**Tube Length** 5,001.26 mm | 196.9 in

**Central Tube Outer Diameter** 11 mm - 15 mm (0.43 in - 0.60 in )

### **Environmental Specifications**

Environmental Space Outdoor

#### Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 1 of 2

# BLK-RCT-A02D0

ROHS

Compliant/Exempted

**UK-ROHS** 

Compliant

