


G35247-000 | FOSC-OC-3DBD1212NN

FOSC® D-TRAY-72 type, DWDM, 8 channels + upgrade port, demux, 1560.61 nm starting wavelength, 200 GHz channel spacing



OBSOLETE

Product Classification

Regional Availability	North America
Product Type	DWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Dimensions

Height	375.92 mm 14.8 in
Width	152.4 mm 6 in
Depth	10.67 mm 0.42 in

Packaging and Weights

Packaging quantity	1
---------------------------	---