

# 760242726XD | 12" Straight Integrated Davit Pole 4G/5G/mmWave



Straight 12inch diameter, Integrated 4G/5G capable, Concealment Pole, with Davit arm

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site

CommScope Integrated Pole that accommodates a Davit light arm above the 4G antenna with future compatibility for mmWave.

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

CommScope Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Integrated pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   White (RAL 9010)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	WIFI
<b>Cooling</b>	Passive Cooling
<b>Radio Compatibility, CommScope</b>	CAP H
<b>Radio Compatibility, Ericsson</b>	1281   220x   440x   4435   5G Expansion module included   6701   6705
<b>Radio Compatibility, Nokia</b>	(2) Airscale micro radios – (radio concealment module)   5G Expansion module included   AEUB   AEWB   AHIA   AHIB   AZRB   Airscale micro

# 760242726XD | 12" Straight Integrated Davit Pole 4G /5G/mmWave

---

**Radio Compatibility Samsung** AT1K01 | AT1K02

**Radios Included** None

## Dimensions

**Pole Height Options** 10.058 m | 33 ft | 10.668 m | 35 ft | 12.192 m | 40 ft

**Depth** 325.12 mm | 12.8 in

**Depth Note** Round

**Pole Diameter** 325.12 mm | 12.8 in

## Electrical Specifications

**Power/Fiber Input** AC load center with OVP and disconnect

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

**Pole Height Options** Overall AGL Standard Height