

NG4-CMDKOJS



NG4access® Cabled Module, singlemode LC/UPC to stub, 216 fiber, rollable ribbon, indoor/outdoor

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	NG4access®
Product Series	LSX NG4
Ordering Note	For fiber modules with custom cable lengths, please contact your local CommScope representative

General Specifications


Configuration Type	NG4 Module to Stub tail
Adapters, quantity, front	108
Body Style	Straight orientation
Cable Color	Yellow
Cable Type	Indoor/outdoor - Rollable Ribbon
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	Stub tail
Polarity	Pairs, straight
Total Fibers, quantity	216
Total Ports, quantity, front	216

NG4-CMDKOJS

Dimensions

Height	13.3 mm 0.524 in
Width	159.9 mm 6.295 in
Depth	101 mm 3.976 in

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
----------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

NG4-CMDKOJS

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

