

760251611XYP | 12" Pole Base 4G/5G w/ Fluted Riser Shaft



Round 12 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, with Straight Fluted riser shaft to house and conceal multiple radios and other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

CommScope Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

Product Classification

| | |
|----------------------|--|
| Portfolio | CommScope® |
| Product Type | Integrated pole |
| Product Brand | Metro Cell |
| Ordering Note | CommScope® standard product with terms |
| Warranty | One year |

General Specifications

| | |
|---|--|
| Antenna Compatibility, CommScope | CommScope Canister Antennas |
| Antenna Compatibility, Other Vendors | ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER |
| Color | Light Gray (RAL 7035) |
| Color Options | Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010) |
| Compatible Foundation Type | Poured Concrete Pre-Cast Concrete |
| Compatible Smart Devices | WIFI |
| Cooling | Passive Cooling |
| Radio Compatibility, CommScope | CAP H |
| Radio Compatibility, Ericsson | 1281 220x 440x 4435 Power Distribution |
| Radio Compatibility, Nokia | (2) Airscale micro radios (Including LAA & CBRS models) (2) Airscale micro radios |

760251611XYP | 12" Pole Base 4G/5G w/ Fluted Riser Shaft

– (radio concealment module) | AHIA | AHIB | AZRB | Power Distribution

Radio Compatibility Samsung

Power Distribution | RT2201-46A | RT4401-48A

Radios Included

None

Dimensions

Height Note

5 ft tall Equipment Base | 5.5 ft tall Radio Concealment Module

Pole Height Options

10.668 m | 35 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 7.925 m | 26 ft | 9.144 m | 30 ft

Width

325.12 mm | 12.8 in

Depth

325.12 mm | 12.8 in

Depth Note

Round

Pole Diameter

325.12 mm | 12.8 in

Electrical Specifications

Power/Fiber Input

AC load center with OVP and disconnect

Material Specifications

Finish Aluminum

Chromate

Finish Concealment Covers

Powder coated

Material Type

Steel

Environmental Specifications

Thermal Compliance

GR-487

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

Pole Height Options

Overall AGL Standard Height