


FGGMPUCRP



Singlemode, MPO12 Unpinned to Unconnectorized, Fiber Trunk Cable Assembly, 288-Fiber, Rollable Ribbon Central Tube, Plenum

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	InstaPATCH® 360
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Color, boot A	Black
Color, connector A	Green
Construction Type	Rollable ribbon
Fibers per Subunit, quantity	12
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Female
Interface, Connector B	Unterminated
Jacket Color	Yellow
Polarity	Method B (LL)
Total Fibers, quantity	288

Dimensions

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 – 999

FGGMPUCRP

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Included Products

- 760239140 P-288-CN-RR-F12YL/8G/99E – Fiber indoor cable, Plenum All-Dielectric Central Tube Rollable Ribbon, 288 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
- 860638318 – MP012, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm