760253133 | 30" Pole Cab 90" Tall Base With Round Shaft



Bottom of the Pole, 30in Square by 90" tall 4G/5G capable Multi Carrier Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Available with Pole Top concealment, mmWave 5G mounting, luminaire arms.

Product Classification

Portfolio CommScope®

Product Type Pole cab
Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Antenna Compatibility, CommScope CommScope Canister Antennas | Panel Antenna

Antenna Compatibility, Other Vendors ACE | AMPHENOL | GALTRONICS | GAMMA NU | JMA | KATHREIN | KMW | ROSENBERG

Color Light Gray (RAL 7035)

Color Options Black (RAL 9005) | Brown (RAL 8014) | Metallic Silver

Compatible Foundation Type Poured Concrete | Pre-Cast Concrete

Compatible Smart Devices Cameras | Digital Signage | Emergency Call Station | Environmental Monitoring | Security Lighting

Cooling Air conditioned | Fan Cooling

Power Supply Compatibility DELTA 2.0 | PSU-AC-08

Radio Compatibility, CommScope CAP H

Radio Compatibility, Ericsson 1281 | 220x | 440x | 4415 | 4426 | 4449 | 4478 | 6701 | 8843 | 8863 | Diplexer

Radio Compatibility, Nokia AEUB | AEWB | AEWD

/AEWE | AHBCA | AHFIA | AHFIB | AHFIC | AHIA | AHIB | AHLBA | AHLBBA | AZRB

Radio Compatibility Samsung AT1K01 | AT1K02 | AT1K0X | Diplexer | RF4402D-D1A | RFV01U-D1A | RFV01U-D2A | RT2

46A | RT4401-48A

Radios Included None

Page 1 of 2



760253133 | 30" Pole Cab 90" Tall Base With Round Shaft

Dimensions

Height 2,286 mm | 90 in

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25

ft | 9.144 m | 30 ft

 Width
 762 mm | 30 in

 Depth
 762 mm | 30 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Input Voltage230-115 VacGenerator ConnectionNo connection

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Pole Height Options Overall AGL Standard Height

