

# 760253092 | OCM8-SP12GLLG-40DB



OCM8 Fiber Optic Splitter Module, Planar, 2x16 Splitter, singlemode, LC /APC, symmetrical split ratio, 4 m pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Europe   India   Latin America   North America
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM8

## General Specifications

<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Distribution Type</b>	2 x 16 splitter
<b>Interface, Input</b>	LC
<b>Interface, Output</b>	LC
<b>Interface Feature, Output</b>	APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Pigtail Length, Input</b>	4 m   13.123 ft
<b>Pigtail Length, Output</b>	4 m   13.123 ft
<b>Pigtail Diameter, Input</b>	1.8 mm   0.071 in
<b>Pigtail Diameter, Output</b>	1.8 mm   0.071 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

