

F1A-HMDM-P-W



FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Male with HELIAX® SureGuard weatherproofing,

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|----------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Series | FSJ1-50A |

General Specifications

| | |
|------------------------------------|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|----------------------------------|--------------------|
| Length | 0.914 m 2.999 ft |
| Cable Assembly Length Range (ft) | 1 – 100 |
| Nominal Size | 1/4 in |

Electrical Specifications

| | |
|---------------------------|----------------------|
| 3rd Order IMD | -107 dBm |
| 3rd Order IMD Test Method | Two +43 dBm carriers |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz | 1.152 | 23.02 |
| 1700–2200 MHz | 1.152 | 23.02 |
| 2200–2700 MHz | 1.152 | 23.02 |

F1A-HMDM-P-W

Jumper Assembly Sample Label



Environmental Specifications

| | |
|------------------------|---|
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |
| Weatherproofing Method | HELIAX® SureGuard weatherproofing boot |