

FPX-2FRH0Z480



FPX Fiber Optic Termination Panel with HMFOC tether, 2RU, 19in, Singlemode, 48 fiber, LC/APC Connector to 4x12 fiber HMFOC, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FPX

General Specifications

Functionality	Patching
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Partially loaded
Interface, front	LC
Interface Feature, front	APC
Patching Capacity, maximum	48
Rack Type	EIA 19 in EIA 23 in
Rack Units	2
Shelf Movement	Sliding
Total Fibers, quantity	48
Total Ports, quantity	48

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in
Cable Stub Length	0 m 0 ft

Material Specifications

Finish	Powder coated
---------------	---------------

FPX-2FRH0Z480

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1