
UJXQXQXTL

Base Product



Ultra Low Loss (ULL) OM4 MPO8 (Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 96-Fiber, Dual Rated (OFNR/LSZH)

Product Classification

| Regional Availability | Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America |
|-----------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber trunk cable assembly |
| Product Brand | Propel SYSTIMAX ULL |
| Ordering Note | For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

General Specifications

| Connector A, quantity | 12 |
|------------------------------|-------------------------|
| Color, boot A | Gray |
| Color, connector A | Aqua |
| Connector B, quantity | 12 |
| Color, boot B | Gray |
| Color, connector B | Aqua |
| Construction Type | Stranded |
| Furcation Color | Aqua |
| Interface, Connector A | MPO-08/UPC Male |
| Interface, Connector B | MPO-08/UPC Male |
| Jacket Color | Aqua |
| Polarity | Method B Enhanced (ULL) |
| Fibers per Subunit, quantity | 8 |
| Total Fibers, quantity | 96 |
| | |

Dimensions

Page 1 of 3


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



UJXQXQXTL

| Breakout Length | 22 in |
|----------------------------------|----------|
| Cable Assembly Length Range (m) | 3 - 305 |
| Cable Assembly Length Range (ft) | 10 - 999 |

Ordering Tree



Mechanical Specifications

| Cable Retention | Strength. | maximum |
|------------------------|-----------|----------|
| | ou engui, | maximani |

11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

| Fiber Mode | Multimode |
|------------|-----------------|
| Fiber Type | OM4, LazrSPEED® |

Environmental Specifications

| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
|-----------------------|--------------------------------------|
| Environmental Space | Dual Rated LSZH/Riser Indoor |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ANATEL | Compliant |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

COMMSCOPE°

UJXQXQXTL

| Included Products | | |
|--------------------------------------|---|---|
| 760248169 N-096-MP-5K-F08AQ/20T/D | - | Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating |
| 860659018 | - | MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm |

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

