


UQG2P2EBH



Ultra Low Loss (ULL) Singlemode G.657.A2, 2X3, MPO24 (Non-Pinned) to MPO24 (Non-Pinned-QSFP), 48-Fiber, Conversion Array, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber conversion array cable assembly
Product Brand	Propel SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Connector A, quantity	2
Color, boot A	Red
Color, connector A	Green
Connector B, quantity	3
Color, boot B	Red
Color, connector B	Green
Construction Type	Stranded
Fibers per Subunit, quantity	24
Furcation Color	Yellow
Interface, Connector A	MPO-24/APC Female
Interface, Connector B	MPO-24/APC Female
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	48

Dimensions

UQG2P2EBH

Breakout Length	12 in 24 in 36 in 48 in 60 in 72 in
Cable Assembly Length Range (m)	3 – 305
Cable Assembly Length Range (ft)	10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0° 4.40 lb @ 90°
--	-------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor Plenum

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

UQG2P2EBH



Included Products

- 760240267 - Plenum MPO Trunk Cable, 48 fiber with 24 fiber subunits
P-048-MP-8G-F24YL
- 860651708 - TeraPEED® MPO Female 24 Fiber Connector, green, 3.6 mm
- 860662281 - MPO24,FEMALE,SM, GREEN,3.0MM