

# FGS-HNTS-1/2-A

---



FiberGuide® Top Support Adjustable C-Bracket Kit, 1/2in for 2x6, 4x4, 4x6in Systems

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Product Feature</b>	Adjustable Height
<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket
<b>Bracket Type</b>	C-bracket
<b>Bracket Installation Type</b>	N/A
<b>Attachment Type</b>	Threaded rod

## Dimensions

<b>Height</b>	306.578 mm   12.07 in
<b>Width</b>	41.148 mm   1.62 in
<b>Length</b>	206.248 mm   8.12 in
<b>Thread Size</b>	1/2 in
<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   51 mm x 152 mm (2 in x 6 in)

## Ordering Tree

# FGS-HNTS-1/2-A

FGS -  -   -   -

## For Section Size

9	<input type="text" value="empty"/>	4 x 4 in, 4 x 6 in
	<input type="text" value="F"/>	4 x 12 in

## For Threaded Rod Size

10	<input type="text" value="1/2"/>	1/2 in
	<input type="text" value="1/2-LP"/>	1/2 in, low profile
	<input type="text" value="12MM"/>	12 mm
	<input type="text" value="12MM-LP"/>	12 mm, low profile
	<input type="text" value="14MM"/>	14 mm
	<input type="text" value="14MM-LP"/>	14 mm, low profile
	<input type="text" value="16MM"/>	16 mm
	<input type="text" value="16MM-LP"/>	16 mm, low profile
	<input type="text" value="5/8"/>	5/8 in
	<input type="text" value="5/8-LP"/>	5/8 in, low profile

11	<input type="text" value="A"/>	Adjustable
----	--------------------------------	------------

## Material Specifications

**Material Type** Carbon steel

## Packaging and Weights

**Included** Hardware

**Packaging quantity** 1

**Weight, net** 1.52 kg | 3.35 lb