


FGS-HNTS-F-5/8-A



FiberGuide® Top Support Adjustable C-Bracket Kit, 5/8in for 4x12in System

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Adjustable Height
Color	Black
Orientation	Horizontal
Section Type	Bracket

Dimensions

Height	304.8 mm 12 in
Width	41.148 mm 1.62 in
Length	384.048 mm 15.12 in
Thread Size	5/8 in
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Ordering Tree

FGS-HNTS-F-5/8-A

FGS - - - - - - -

For Section Size

9	<input type="text" value="empty"/>	4 x 4 in, 4 x 6 in
	<input type="text" value="F"/>	4 x 12 in

For Threaded Rod Size

10	<input type="text" value="1/2"/>	1/2 in
	<input type="text" value="1/2-LP"/>	1/2 in, low profile
	<input type="text" value="12MM"/>	12 mm
	<input type="text" value="12MM-LP"/>	12 mm, low profile
	<input type="text" value="14MM"/>	14 mm
	<input type="text" value="14MM-LP"/>	14 mm, low profile
	<input type="text" value="16MM"/>	16 mm
	<input type="text" value="16MM-LP"/>	16 mm, low profile
	<input type="text" value="5/8"/>	5/8 in
	<input type="text" value="5/8-LP"/>	5/8 in, low profile

11	<input type="text" value="A"/>	Adjustable
----	--------------------------------	------------

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 2.517 kg | 5.55 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

