

# CB-12-50

---



Cable Banding, Bulk, 1/2 in x 50 ft Reel (uses CB-LH-25 Locking Heads - not incl)

## Product Classification

<b>Product Type</b>	Banding
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Adapter
<b>Color</b>	Black
<b>Mounting</b>	Round member

## Dimensions

<b>Width</b>	12.7 mm   0.5 in
<b>Length</b>	15.24 m   50 ft
<b>Material Thickness</b>	1.524 mm   0.06 in

## Material Specifications

<b>Material Type</b>	Heat-stabilized weather resistant acetal
----------------------	--

## Mechanical Specifications

<b>Tensile Force</b>	1,112.055 N   250 lbf
----------------------	-----------------------

## Environmental Specifications

<b>Installation temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Operating Temperature</b>	-65 °C to +90 °C (-85 °F to +194 °F)

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# CB-12-50

---

CHINA-ROHS	Below maximum concentration value
CSA	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

