

# L4A-KMNM-P

---

LDF4-50A SureFlex® Jumper with interface types 4.1-9.5 DIN Male and N Male



## Product Classification

<b>Product Type</b>	SureFlex® Premium, static PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	LDF4-50A

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	4.1-9.5 DIN Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Cable Assembly Length Range (ft)</b>	1 – 100
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers per IEC 62037
<b>3rd Order IMD, typical</b>	-112 dBm
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-34 dB

## Jumper Assembly Sample Label

# L4A-KMNM-P

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition