

PTS1-XMPDM-D



PTS1-50-P SureFlex® Jumper with interface types NEX10 Male and 7-16 DIN male

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	PTS1-50-P

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Cable Assembly Length Range (m)	1 – 30
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD Static	-116 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
10–18000 MHz	1.671	12

Jumper Assembly Sample Label

PTS1-XMPDM-D



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition