

# BUDI-R24NP0159A | BUDI-R24NP0159A



BUDI™ Rapid Terminal, 24-position, SC/UPC, Indoor plenum cable, MPO at far end, 50 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   Europe   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Rapid distribution terminal
<b>Product Brand</b>	BUDI™   RapidReel®
<b>Product Series</b>	BUDI-R
<b>Warranty</b>	For more information, please consult our Product Warranty guidelines

## General Specifications

<b>Functionality</b>	Patching   Slack storage
<b>Adapters, quantity</b>	24
<b>Cable Entry Location</b>	Bottom
<b>Cable Sealing Type</b>	Gasket/grommet configuration
<b>Cable Type</b>	Indoor - Stranded
<b>Color</b>	Gray
<b>Distribution Type</b>	24 ports
<b>Interface</b>	SC/UPC
<b>Interface, stub</b>	MPO
<b>Lock Type</b>	Security screw
<b>Mounting</b>	Wall mount
<b>Port, quantity</b>	24

## Dimensions

<b>Height</b>	270 mm   10.63 in
<b>Width</b>	214 mm   8.425 in

# BUDI-R24NP0159A | BUDI-R24NP0159A

---

**Depth** 125 mm | 4.921 in

**Cable Length** 15 m | 49.213 ft

**Enclosure Size** Small

## Material Specifications

**Material Type** Polycarbonate ABS (PC-ABS)

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2

## Environmental Specifications

**Operating Temperature** -40 °C to +65 °C (-40 °F to +149 °F)

**Environmental Space** Indoor/Outdoor

**Flammability Rating** UL 94 V-0

**Qualification Standards** IEC 61753-1 | UL

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Carton

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines