

SSH-411



SnapTak PIM-Guard Adjustable Hanger, Gen 2. Fits 4.0 mm to 11.0 mm Cables – PIM Free Polymer Construction. No Grommets Required

Product Classification

Product Type	Hanger kit
Product Brand	SnapTak PIM-Guard
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Maximum Stack Height, Coaxial	3
Height	42.8 mm 1.685 in
Width	32 mm 1.26 in
Length	46.7 mm 1.839 in
Compatible Cable Diameter Range	4–11 mm
Compatible Diameter, maximum	11 mm 0.433 in
Compatible Diameter, minimum	4 mm 0.157 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

SSH-411

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 3.1 cm | 1.22 in

Width, packed 20.3 cm | 7.992 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 0.36 kg | 0.794 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power