

MC-DPM35-96



GroundSmart® Monopole Co-location Dual Pipe Mount Kit, 4 ft 9 in face, includes pipe

Product Classification

Product Type Co-location dual pipe mount kit

General Specifications

Pipe, quantity 2

Sectors, quantity 1

Dimensions

Height 2,438.4 mm | 96 in

Face Width 1.463 m | 4.8 ft

Width 1,447.8 mm | 57 in

Length 355.6 mm | 14 in

Pipe Length 2,438.4 mm | 96 in

Pipe Outer Diameter 88.9 mm | 3.5 in

Stand-off Distance 355.6 mm | 14 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Criteria Four 72 in x 8 in panel antennas per sector

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Dual pipe frames | Pipe mounts

Packaging quantity 1

Weight, net 99.79 kg | 220 lb

MC-DPM35-96

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code