

# MC-PK8-C

---



Low-Profile Co-location Platform Kit, 8 ft face, 12 in to 38 in OD, (9) 2-3 /8" OD x 72" Pipes, with Support Rail Kit

Please contact ANDREW for detailed drawings prior to ordering.

## Product Classification

<b>Product Type</b>	Monopole platform kit
<b>Ordering Note</b>	NSTD445 Compliant

## General Specifications

<b>Mounting</b>	Monopole, 305–965 mm (12–38 in) OD
<b>Pipe, quantity</b>	9
<b>Sectors, quantity</b>	3

## Dimensions

<b>Height</b>	1,828.8 mm   72 in
<b>Face Width</b>	2.438 m   8 ft
<b>Width</b>	2,438.4 mm   96 in
<b>Pipe Length</b>	1,828.8 mm   72 in
<b>Face Support Pipe Diameter</b>	88.9 mm   3.5 in
<b>Mounting Diameter, maximum</b>	965.2 mm   38 in
<b>Mounting Diameter, minimum</b>	304.8 mm   12 in
<b>Pipe Outer Diameter</b>	60.325 mm   2.375 in
<b>Stand-off Distance</b>	914.4 mm   36 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact your local ANDREW representative
<b>Wind Rating Test Method</b>	TIA/EIA-222

# MC-PK8-C

---

## Packaging and Weights

<b>Included</b>	Hardware   Plain end pipes (9)   Platform   Rail   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	622.782 kg   1373 lb

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--