## BUDI-R



#### BUDI™ Rapid Fiber Optic Wall mount Enclosure

The  $BUDI^{M}$  rapid fiber distribution terminal (BUDI-R) is a compact, high density, fiber box solution, designed to speed up installation requirements on the customer premises.

Utilizing the RapidReel® fiber cable spool, the BUDI-R deploys up to 1,000 feet of indoor plenum cable or I/O riser single cable. The multi-fiber cable terminates to multi-fiber push-on (MPO) connectors, hardened multi-fiber optical connectors (HMFOC) or connectors less option for splicing applications (Dummy MPO with pulling eye included), ensuring fast cable routing and simplified handling by technicians. For service turn-up, the BUDI-R features up to 24 fiber ports for fast, plug-and-play drop cable connections using wrap-around ports.

#### Benefits:

- Compact plastic design: 4.9 in (124.4 mm) x 8.4 in (213.4 mm) x 10.63 in (270 mm).
- Indoor and outdoor applications (IP54 and UL94)
- Equipped with 24 adapter ports. Cable terminated to MPO or HMFOC connectors. Connector less option also available
- RapidReel fiber cable spool deploys up to 50 ft (15 m) of stubbed cable. External spool included for cable lengths over 50 ft (15 m) up to 1,000 ft (305 m). Standard cable length increments of 100 ft.
- Cost savings: RapidReel fiber cable spool reduces upfront deployment costs by eliminating site survey inspections, reducing labor hours and streamlining cable requirements
- Reduced labor: Preconnectorized plug-and-play solution eliminates splice labor requirements and speeds network construction.
- Space savings: Compact MPO connector design and multifiber cable is ideal for high-density intrafacility applications. Excess fiber
  is stored within unit. No additional enclosures are required for intrafacility applications
- Hinge mechanism locks cover in open position for unhindered technician access
- Removable door and security captive screw (216) included
- External fiber management accessory (skirt) available

#### **Product Classification**

Regional Availability Australia/New Zealand | Europe | North America

Portfolio CommScope®

Product Type Rapid distribution terminal

Product Brand BUDI™ | RapidReel®

Product Series BUDI-R

Warranty For more information, please consult our Product Warranty guidelines

#### General Specifications

Functionality Patching | Slack storage

Adapters, quantity 24

Cable Entry Location Bottom

**COMMSCOPE®** 

## **BUDI-R**

Cable Sealing Type Gasket/grommet configuration

**Color** Gray

**Distribution Type** 24 ports

Interface SC/APC | SC/UPC

Interface, stub HMFOC | MPO | No connector

Lock Type Security screw

Mounting Wall mount

Port, quantity 24


#### **Dimensions**

 Height
 270 mm | 10.63 in

 Width
 214 mm | 8.425 in

 Depth
 125 mm | 4.921 in

### Ordering Tree



## Material Specifications

Material Type Polycarbonate ABS (PC-ABS)

Optical Specifications

**COMMSCOPE®** 

# **BUDI-R**

Fiber ModeSinglemodeFiber TypeG.657.A2

### **Environmental Specifications**

**Operating Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +65 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +149 \, ^{\circ}\text{F})$ 

**Environmental Space** Indoor/Outdoor

Flammability Rating UL 94 V-0

Qualification Standards IEC 61753-1 | UL

### Packaging and Weights

Packaging quantity 1

Packaging Type Carton

#### \* Footnotes

Warranty For more information, please consult our Product Warranty guidelines