



Product Classification

Regional Availability Asia

Product Type

NETCONNECT®

Twisted pair cable

General Specifications

ANSI/TIA Category 6

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singles Solid
Conductors, quantity 8

Jacket Color Blue
Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class E

Dimensions

 Cable Length
 304.8 m | 1000 ft

 Diameter Over Jacket, nominal
 5.588 mm | 0.22 in

Conductor Gauge, singles 24 AWG

Electrical Specifications

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery

of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1,

CENELEC EN 50174-2 or TIA TSB-184-A

COMMSCOPE®

1859620-6

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefinJacket MaterialPVC

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Packaging and Weights

Packaging Type Reel in box

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

