

MTC4078HD

Heavy Duty Stiff Arm / Tieback, includes 2-7/8" OD x 198" pipe



Product Classification

Product Type Stiff arm mount

General Specifications

Mounting Round and angle legs

Pipe, quantity 1

Dimensions

Length 5,029.2 mm | 198 in

Pipe Length 5,029.2 mm | 198 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 48.26 mm | 1.9 in

Pipe Outer Diameter 71.12 mm | 2.8 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Attachment hardware | Pipe

Packaging quantity 1

Weight, net 50.349 kg | 111 lb