

# L4A-HPXMHM-3M

---

LDF4-50A SureFlex® Jumper with interface types Nex10 Male and 4.3-10 Male, 3 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	SureFlex® HP, HELIAX® performance
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	LDF4-50A

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	NEX10 Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	3 m   9.843 ft
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers
<b>3rd Order IMD, typical</b>	-116 dBm
<b>DTF, Connector A</b>	-32 dB
<b>DTF, Connector B</b>	-34 dB

## VSWR/Return Loss

# L4A-HPXMHM-3M

Frequency Band	VSWR, typical	Return Loss, typical (dB)
680–960 MHz	1.065	30
1700–2200 MHz	1.083	28
2200–2700 MHz	1.106	26
3400–3800 MHz	1.222	20

## Jumper Assembly Sample Label



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Included Products

- LDF4-50A – LDF4-50A, HELIAX<sup>®</sup> Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket Halogen free jacketing non-fire-retardant (General propose cable for outdoor use only)