760256445 | TENIO-B6-FLAT



TENIO™ B6- Distribution closure FLAT cable kit with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

This kit is designed to splice HST hardened terminals. Kitted with flat seal kits out, and a standard round kit for incoming feeder. Cabletermination units are included as well as a MOBRA bracket suitable for use with PIA chambers. Fibre trays and seal kits are preassembled into the closure in the factory to reduce engineering time in the field.

Product Classification

Regional Availability EMEA | Latin America

Product Type Single-ended, rectangular fiber closure

Product Brand TENIO™
Product Series TENIO

General Specifications

Cable Entry Drop Port StyleGel blockCable Entry Main Port StyleGel block

Cable Ports Quantity, total6 multi-out ports (30 cables)

Cable Sealing TypeCompressed gel

Closure Sealing Type Side latch

Closure Style Single-ended

Color Black

Flash Test Valve Pre-installed

Mounting Wall

Network Area Type Distribution | Drop

Splice Tray Included, quantity 12

Splice Tray Type Included 12-fiber, single element

Splices per Tray, quantity 12
Splicing Capacity, Single Fusion, maximum 144

Splicing Type, Supported Single fusion

Dimensions

COMMSC PE°

760256445 | TENIO-B6-FLAT

 Height
 230 mm | 9.055 in

 Width
 134 mm | 5.276 in

 Length
 389 mm | 15.315 in

 Main Cable Diameter, maximum
 16 mm | 0.63 in

Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental SpaceBelow ground| BuriedQualification StandardsIEC 61300, 2 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity 1

Packaging TypeBox| CartonWeight, net1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760244933 – Fiber Closure Cable Termination Unit, Large for up to 16 mm diamter cables

CTU-L

760250714 – TENIO™ Mounting bracket for arm mounting

TENIO-MOBRA-TUBE-45x45

CV6797-000 – TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet

TENIO-SKG3-7/10

CV6800-000

TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12

TENIO-B6-S12-12-V heat shrink splice protectors (SMOUV 45 mm), with test valve

CW8862-000 – TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black TENIO-SKG-DUMMY

COMMSCOPE®

760256445 | TENIO-B6-FLAT

EH1674-000 TENIO-SKG3-3/5X6/9 – TENIO™ Cable Gel Seal kit, 3 flat cable outlets, 3/5 mm x 6/9 mm diameter per cable outlet

COMMSCOPE®