PM-RU3T



Universal RRU Tower Mount Kit for Straight or Tapered legs

Product Classification

Product Type Remote radio head unit mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in)

Tower Taper Non-tapered | Tapered

Dimensions

 Height
 609.6 mm | 24 in

 Length
 304.8 mm | 12 in

 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Hardware

Packaging quantity 2

Weight, net 38.918 kg | 85.8 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted

UK-ROHS Compliant



