

RK-36-3S



Monopole Load Distribution Reinforcement Kit, 3 Sector, 10" to 30" OD, 36" Kicker

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Sectors, quantity 3

Dimensions

Height 254 mm | 10 in

Length 914.4 mm | 36 in

Mounting Diameter, maximum 762 mm | 30 in

Mounting Diameter, minimum 254 mm | 10 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Attachment hardware | Ring mount

Packaging quantity 1

Weight, net 111.13 kg | 245 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

RK-36-3S

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code