

SA-1TR



PIM-Guard® Multifunction Adapter that threads into 3/8" & 1/2" bolts & U-bolts or snaps into 3/4" holes. One 3/4" hole for Snap-in style hangers, supporting three stacks for 4-17mm or two stacks for 26-40mm cables

- Snaps into 3/4" holes to provide 1 inch standoff
- Threads into 3/8" & 1/2" bolts & U-bolts to launch hangers
- Snaps between SnapTak hangers to provide 360 degree hanger rotation

Product Classification

Product Type	Stand-off mount
Product Brand	PIM-Guard®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Adapter Type	Stand-off adapter
Color	Black
Mounting	1/2 in threads 3/4 in through hole 3/8 in threads

Dimensions

Height	25.908 mm 1.02 in
Width	28.956 mm 1.14 in
Length	0.03 m 0.1 ft

Material Specifications

Material Type	Engineered polymer
---------------	--------------------

Mechanical Specifications

Maximum Loading	Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411, SSH-1117
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
Environmental Strength Capability	Double cable weight

Designed, manufactured and/or distributed under this quality management system