

F4-CLAMP-4B



KwikClamp™ Hanger for 1/2 in superflexible coaxial cable, quadruple stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	4
Height	192 mm 7.559 in
Width	31 mm 1.22 in
Length	42 mm 1.654 in
Compatible Diameter, maximum	13.2 mm 0.52 in
Compatible Diameter, minimum	10.4 mm 0.409 in
Nominal Size	1/2 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

F4-CLAMP-4B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 30

Weight, gross 4.4 kg | 9.7 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power