

# R8-CLAMP-4B



KwikClamp™ Hanger for RG8 cable, quadruple stack; includes hardware

## Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron   3–25 mm flat plate   Round Member 8–25 mm

## Dimensions

Maximum Stack Height	4
Height	192 mm   7.559 in
Width	32 mm   1.26 in
Length	42 mm   1.654 in
Compatible Diameter, maximum	12 mm   0.472 in
Compatible Diameter, minimum	9 mm   0.354 in
Nominal Size	3/8 in
Hanger Spacing, maximum	1.83 m   6.004 ft

## Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

# R8-CLAMP-4B

---

## Material Specifications

**Material Type** Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 45

**Weight, gross** 8.97 kg | 19.775 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power