



FACT® Fiber Optic Patch/Splice Panel, 2E high, 96-port, singlemode, loaded with LC/APC Duplex adapters and C-grade pigtails, SMOUV splice tray type, 15m indoor Micro-Tube cable, G657A1, yellow jacket, EN50575 CPR Cable EuroClass Dca, right-hand patch

- Designed for use with the all-purpose all-front-access FIST-GR3 fiber frames supporting up to 2,688 LC or 1,344 SC connections in a single frame
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel, with indoor cable
<b>Product Brand</b>	FACT®
<b>Product Series</b>	FACT

## General Specifications

<b>Functionality</b>	Patching
<b>Application</b>	Compatible with FIST-GR3-style frames
<b>Body Style</b>	Right-hand patch
<b>Cable Stub Type</b>	Indoor, microcable
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	Stub tail
<b>Patch Cord Routing</b>	Right sided
<b>Patching Capacity, maximum</b>	96
<b>Rack Type</b>	EIA 19 in

# 760254303 | FACT-2ERHPL2S-150CK

---


<b>Rack Units</b>	1.4
<b>Shelf Movement</b>	Sliding
<b>Splicing Capacity, maximum</b>	96
<b>Splicing Type</b>	SMOUV
<b>Total Ports, quantity</b>	96
<b>Transmission Standards</b>	ETSI EN 300 019-1-3   IEC 61300-3-30

## Dimensions

<b>Height</b>	61.9 mm   2.437 in
<b>Width</b>	524 mm   20.63 in
<b>Depth</b>	283 mm   11.142 in
<b>Cable Length</b>	15 m   49.213 ft

## Ordering Tree

# 760254303 | FACT-2ERHPL2S-150CK



## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A1
<b>Performance Grade</b>	Standard C grade
<b>Insertion Loss, maximum</b>	0.25 dB
<b>Return Loss, minimum</b>	60 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-20 °C to +85 °C (-4 °F to +176 °F)
<b>EN50575 CPR Cable EuroClass</b>	Dca

# 760254303 | FACT-2ERHPL2S-150CK

---

**Flammability Rating** UL 94 V-0

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## \* Footnotes

**Performance Grade** Guarantee to meet IEC 61755-1 Random Mating requirement