

4


3

2

1

NOTES:

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A		INITIAL RELEASE	MJP	10/31/2023



<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>										
TOLERANCES					SAP MATERIAL MASTER					
0 PLACE		X ± .25		2 PLACE		.XX ± 0.06				
1 PLACE		.X ± 0.12		ANGLES		± 2°				
FINISH GALV A123					MATERIAL A36, A568, A529					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.3M-1994	CE	ACG	04/11/05	<b>12' X 20' PLATFORM LAYOUT</b>						
	RW	MC1107	02/26/2019							
	RV		02/27/2019							
	AD	---	02/27/2019							
	RE	MC1107	02/27/2019							
ECN 008000033964				SCALE	DOCUMENT NO.					
				1:32	<b>EQ-P1220 LAYOUT</b>					
SIZE	WORK AREA	24		MODEL			DRAWING			SHEET
<b>C</b>				VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1
				00	RE	A	01	RE	A	

DENSITY	0.28	lbs/in <sup>3</sup>
MASS	8915.37	lbs
VOLUME		in <sup>3</sup>
SURFACE AREA		in <sup>2</sup>
HEIGHT		
LENGTH		
WIDTH		

© 2019 CommScope, Inc. Confidential

4

3

2

1

A

A