

WP-TM-B



Wood Pole Top Mast, 7 in to 14 in wood poles

Product Classification

Product Type Wood pole mount

General Specifications

Mounting Wood pole, 177.8–355.6 mm (7–14 in) OD

Pipe, quantity 0

Sectors, quantity 1

Dimensions

Height 14 in | 355.6 mm

Length 96 in | 2,438.4 mm

Mounting Diameter, maximum 14 in | 355.6 mm

Mounting Diameter, minimum 7 in | 177.8 mm

Pipe Outer Diameter 2.4 in | 60.96 mm

Mounting Circumference, maximum 13.9 in | 353.06 mm

Mounting Circumference, minimum 6.9 in | 175.26 mm

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Mast | Wood pole mount

Packaging quantity 1

Weight, net 225.1 lb | 102.104 kg

WP-TM-B

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code