

CSC6-B4E1A1CA000



NOVUX™ CSC150 Compact Fiber Closure, ANT splice trays with island, splice/patch, 8 LC/APC duplex adapters, no pigtails, no splitters, no mounting bracket, gray

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Single-ended, rectangular fiber closure |
| Product Brand | NOVUX™ |
| Product Series | CSC 150 |

General Specifications

| | |
|--|-------------------|
| Cable Sealing Type | Compressed gel |
| Closure Sealing Type | Hinged with latch |
| Closure Style | Single-ended |
| Color | Gray |
| Mounting | Pole Wall |
| Port Type | LC/APC |
| Port, quantity | 16 |
| Splicing Capacity, maximum | 72 |
| Splicing Capacity, Single Fusion, maximum | 72 |
| Splitter Type | No splitter |
| Splitter, quantity | 0 |

CSC6-B4E1A1CA000

Dimensions

| | |
|---------------|---------------------|
| Height | 357 mm 14.055 in |
| Width | 185.4 mm 7.299 in |
| Depth | 115 mm 4.528 in |

Environmental Specifications

| | |
|----------------------------|---------------|
| Environmental Space | Outdoor |
| UV Resistance | UV stabilized |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |
| Packaging Type | Box Carton |