

# FD3-AE288J00GGBP4-US



FDH 3000 Small Fiber Distribution Cabinet, 288F, SC/APC, no splitters, single armor loose tube, 100 ft, 48F, Build America Buy America (BABA)

- \*CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | North America                                 |
| <b>Product Type</b>          | Fiber distribution hub                        |
| <b>Product Series</b>        | FDH 3000                                      |
| <b>Government Funding</b>    | Build America Buy America (BABA) coming soon* |

## General Specifications

|  |                             |
|--|-----------------------------|
| <b>Access</b>                                  | Front                       |
| <b>Cable Type</b>                              | Armored - Single Loose Tube |
| <b>Color</b>                                   | Putty white                 |
| <b>Distribution Cables, quantity</b>           | 1                           |
| <b>Distribution Ports, quantity</b>            | 288                         |
| <b>Fibers per Distribution Cable, quantity</b> | 288                         |
| <b>Fibers per Feeder Cable, quantity</b>       | 48                          |
| <b>Interface, Input</b>                        | SC                          |
| <b>Interface Feature, Input</b>                | APC                         |
| <b>Mounting</b>                                | Pad                         |
| <b>Splitter Slots, quantity</b>                | 12                          |

## Dimensions

|                       |                    |
|-----------------------|--------------------|
| <b>Height</b>         | 914 mm   35.984 in |
| <b>Width</b>          | 686 mm   27.008 in |
| <b>Depth</b>          | 457 mm   17.992 in |
| <b>Cable Length</b>   | 30.48 m   100 ft   |
| <b>Enclosure Size</b> | Small              |

# FD3-AE288J00GGBP4-US

---

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Aluminum      |

## Environmental Specifications

|                            |              |
|----------------------------|--------------|
| <b>Environmental Space</b> | Above ground |
|----------------------------|--------------|

## Packaging and Weights

|                           |        |
|---------------------------|--------|
| <b>Packaging quantity</b> | 1      |
| <b>Packaging Type</b>     | Pallet |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>   |
|---------------|---|
| CHINA-ROHS    | Above maximum concentration value   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted  |
| UK-ROHS       | Compliant/Exempted  |

