

DFJ-2S5-2G



HELIAX® Discrete, 2 single mode fiber, 5 mm, LSZH cable. Plug and play DLC GEN 1.5 to DLC.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	DFJ
Ordering Note	CommScope® Standard Product in Europe

General Specifications

Construction Type	Discrete fiber tail
Interface, Connector A	DLC plug and play GEN1.5
Interface Feature, connector A	Standard
Interface Body Style, connector A	Flex angle
Interface, Connector B	DLC plug and play GEN1.5
Interface Feature, connector B	Standard
Interface Body Style, connector B	Flex angle
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Cable Assembly Length Range (m)	1 – 15
Diameter Over Jacket	5 mm 0.197 in

Material Specifications

Jacket Material	Low Smoke Zero Halogen (LSZH)
------------------------	-------------------------------

Mechanical Specifications

Minimum Bend Radius	54 mm 2.126 in
Minimum Bend Radius, furcation	30 mm 1.181 in

Optical Specifications

DFJ-2S5-2G

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Outdoor

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)