


MP-PP13M4-B



PIM Optimized Adjustable 4-Sector Monopole Platform with 13ft Face - 2-7/8in OD Face Pipes & Top Rail - No Antenna Pipes Included

Product Classification

Product Type	Co-location platform
Product Brand	PIM-guard

General Specifications

Mounting	Monopole, 381–1143 mm (15–45 in) OD
Pipe, quantity	0
Sectors, quantity	4

Dimensions

Face Width	3,962 mm 13 ft
Platform Width	3,962.4 mm 156 in
Width	3,962.4 mm 156 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Mounting Diameter, maximum	1,143 mm 45 in
Mounting Diameter, minimum	381 mm 15 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222
--------------------------------	-------------

Packaging and Weights

Included	Platform Rail Ring mount
-----------------	------------------------------

MP-PP13M4-B

Packaging quantity 1
Weight, net 1,925.214 kg | 4,244.37 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

