

A-100329

Base Product



Link ac Cabinet, Mark 4

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type	Power supply enclosure
Ordering Note	For UK region only

General Specifications

Access	Front door
Batteries Supported	0
Cabinet Type	Integrated cabinet
Color	Green Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Cooling	175 mm fan (1)
Door Security	European profile cylinder
Doors, quantity	2
Mounting	Plinth Root
Rack Type	EIA 19 in
Rack Units	13

Dimensions

Height	1524 mm 60 in
Width	609.6 mm 24 in
Depth	508 mm 20 in

Electrical Specifications

Input Power Supply	100 A
ac Distribution Type	20-way plastic enclosure
dc Distribution Type	8-way dc panel Power supply unit
Generator Connection	No connection
Power Phase	Single

A-100329

Rectifier Power	800 W
Rectifiers, quantity	2
Voltage	230 Vac

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Environmental Specifications

Qualification Standards	IEC 60529: 2001 IEE Wiring Regulations BS 7671 IP55
--------------------------------	---------------------------------------------------------

Packaging and Weights

Included	-48V DC Power supply unit Brackets Cooling Installation Kit Power Distribution
Weight, net	150.139 kg 331 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system