

A-100573

Base Product



Pogona Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type	Micro cell site enclosure
Ordering Note	For UK region only

General Specifications

Access	Front door Side door
Batteries Supported	0
Cabinet Type	Integrated cabinet
Color	Gray Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Cooling	175 mm fan (2)
Door Security	Swing handle with European profile cylinder
Doors, quantity	3
Mounting	Plinth Root
Rack Type	EIA 19 in
Rack Units	12

Dimensions

Height	1,041.4 mm 41 in
Width	1,219.2 mm 48 in
Depth	406.4 mm 16 in

Electrical Specifications

Input Power Supply	32 A
ac Distribution Type	6-way plastic enclosure
dc Distribution Type	Power supply unit
Generator Connection	No connection
Power Phase	Single

A-100573

Rectifier Power	2000 W
Rectifiers, quantity	2
Voltage	230 Vac

Material Specifications

Finish	Powder coated
Material Type	Stainless steel

Environmental Specifications

Qualification Standards	IEC 60529: 2001 IEE Wiring Regulations BS 7671 IP55
--------------------------------	---

Packaging and Weights

Included	-48V DC Power supply unit Brackets Cooling Installation Kit Power Distribution
Weight, net	140.16 kg 309 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system