

1-2122145-1 | FMS-K-1-B-I-S5D-6-IN99-6-SP



FMS Fiber Optic Termination/Splice Panel, 1U, 19 in, 6 SC/UPC, multimode, OM2, black

OBSOLETE

This product was discontinued on: March 1, 2018

Product Classification

| | |
|------------------------------|--------------------------|
| Regional Availability | India |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Series | FMS |

General Specifications

| | |
|--|------------------------------------|
| Functionality | Patching Splicing |
| Body Style | Symmetrical |
| Cable Exit Location | Rear, left side Rear, right side |
| Color | Black |
| Color, front | Black |
| Growth Configuration | Partially loaded |
| Interface, front | SC/UPC |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |
| Splice Trays Included, quantity | 1 |
| Splicing Type | Heat shrink, single fiber fusion |
| Total Ports, quantity | 6 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
|---------------|--------------------|

1-2122145-1 | FMS-K-1-B-I-S5D-6-IN99-6-SP

| | |
|--------------|--------------------|
| Width | 482.6 mm 19 in |
| Depth | 320 mm 12.598 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|--------------------------------|-----------|
| Fiber Mode | Multimode |
| Fiber Type | OM2 |
| Insertion Loss, maximum | 0.3 dB |
| Return Loss, minimum | 45 dB |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |