

Fiber Optic Termination Panel, 3U, 19 in, unloaded, 48-fiber, black

## OBSOLETE

This product was discontinued on: December 31, 2017

### Replaced By:

760231498  
SD-4U-FX

Standard Density 4U fixed Panel, accepts (12) LGX/1000 style footprint modules or panels, providing up to 144 duplex LC ports

## Product Classification

<b>Regional Availability</b>	Asia   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel

## General Specifications

<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	3
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	304.8 mm   12 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Packaging and Weights

# 559614-2

---

**Included** Mounting hardware  
**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

