

# 760005629 | iP-600B-12-SC-MMF



iPatch® 600B Sliding Multimode Intelligent Fiber Panel, SC 12 port duplex

## OBSOLETE

This product was discontinued on: December 31, 2012

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	iPatch®

## General Specifications

<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	SC
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	12

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	317.5 mm   12.5 in

## Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)
----------------------	--

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
------------------------------	-------------------------------------

# 760005629 | iP-600B-12-SC-MMF

---

<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ACMA   CE   CSA   UL

## Packaging and Weights

<b>Included</b>	Cover   Four #12-24 mounting screws   Instruction sheet   One piece double sided tape   Shelf   Two cable fittings, liquid tight   Two cable tie holders, flat   Two cable ties   Two wire retainers
<b>Packaging quantity</b>	1
<b>Weight, net</b>	2.631 kg   5.8 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

