

# 760109884 | 360DM-24LC-LS



360G2 Multimode OM4 Standard Module, 24 LC fibers (12 duplex ports)

## OBSOLETE

This product was discontinued on: June 30, 2019

### Replaced By:

760206532

360DMis-24LC-LS

G2 LL Multimode OM4 MPO 12 distribution module, 24 LC to 2x12f MPO's pinned, internal shutters

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Fiber module

## General Specifications

### Functionality

Breakout

### Adapters, quantity, front

12

### Adapters, quantity, rear

2

### Color, front

Aqua

### Color, rear

Gray

### Data Module Type

Standard

### Intelligence Type

iPatch® ready

### Interface, front

LC/UPC

### Interface, rear

MPO

### Interface Feature, rear

Pinned | Reduced footprint

### Shuttered

Yes

### Total Fibers, quantity

24

### Total Ports, quantity, front

24

## Dimensions

# 760109884 | 360DM-24LC-LS

---

<b>Height</b>	30.48 mm   1.2 in
<b>Width</b>	91.44 mm   3.6 in
<b>Depth</b>	116.84 mm   4.6 in

## Optical Specifications

<b>Fiber Type</b>	OM4, LazrSPEED® 550
<b>Insertion Loss Change, mating</b>	0.3 dB
<b>Insertion Loss Change, temperature</b>	0.3 dB

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

<b>Insertion Loss Change, mating</b>	Maximum insertion loss change after 500 matings
<b>Insertion Loss Change, temperature</b>	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)