


760109967 | 360DM-12SC-LS



G2 LL Multimode OM4 MPO 12 distribution module, 12 SC to 1x12f MPO pinned, dust plugs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	G2

General Specifications

Functionality	Breakout
Color, front	Aqua
Color, rear	Gray
Interface, front	SC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up Pinned
Polarity	Method B
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	26 mm 1.024 in
Width	95 mm 3.74 in
Depth	117.7 mm 4.634 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4

760109967 | 360DM-12SC-LS

Insertion Loss, maximum 0.93 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.113 kg | 0.249 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

