



## iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	RJ45 patch panel
<b>Product Brand</b>	iPatch®   imVision®

### General Specifications

<b>ANSI/TIA Category</b>	6   6A
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Panel Style</b>	Straight
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	24

### Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	25.4 mm   1 in

### Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing

# 760073866 | iP-M4200i-24

---

**Flammability Rating** UL 94 V-0

**Safety Standard** ACMA | CE | UL | cUL

## Packaging and Weights

**Included** Cable management bar | Four #12-24 dog point mounting screws | Information outlet removal tool | Instruction sheet | Panel | Two #12 washers | Two #12-24 screws

**Packaging quantity** 1

**Weight, net** 0.68 kg | 1.5 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted