



SYSTIMAX 360™ iPatch® PATCHMAX® Upgrade Kit, 24 port, 10 pack

OBSOLETE

This product was discontinued on: July 1, 2011

Replaced By:

760152306 SYSTIMAX 360™ iPatch® Upgrade Kit for PATCHMAX Panel, 2U, 24 Port, 10 pack
360-iP-UP-KIT-PMAX-2U-24

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category

6 | 6A

Color

Cool gray

Intelligence Type

iPatch® upgrade kit

Panel Style

Straight

Total Ports, quantity

24

Wiring

T568A | T568B

Dimensions

Height

16 mm | 0.63 in

Compatible Diameter Over Dielectric, minimum

4.775 mm | 0.188 in

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

760130419 | 360-iP-UP-KIT-PMAX-24

Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

Insulation Resistance, minimum

500 MOhm

Material Specifications

Material Type

Acrylonitrile butadiene styrene (ABS) | Polycarbonate

Environmental Specifications

Operating Temperature

-5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

Up to 95%, non-condensing

Flammability Rating

UL 94 V-0

Safety Standard

ACMA | CE | UL | cUL

Packaging and Weights

Packaging quantity

10

Weight, net

2.087 kg | 4.6 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

