

# 760243043 | DM12iP-12LC-LS-ULL



G2 ULL Multimode OM4 MPO-12 Distribution Module, 1x12F MPO unpinned to 12F LC Aqua, Method B Enhanced, iPatch Ready

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	SYSTIMAX ULL

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	1
<b>Color, front</b>	Aqua
<b>Color, rear</b>	Aqua
<b>Data Module Type</b>	G2
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	LC/UPC
<b>Interface Feature, front</b>	Dust caps
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Key up   MPO Non-Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	12

## Dimensions

<b>Height</b>	26.42 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in
<b>Depth</b>	117.35 mm   4.62 in

## Optical Specifications

# 760243043 | DM12iP-12LC-LS-ULL

---

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM4, LazrSPEED® 550
<b>Insertion Loss, maximum</b>	0.35 dB

## Environmental Specifications

<b>Qualification Standards</b>	TIA/EIA-568-C.3
<b>Safety Standard</b>	cUL US 1863

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

