

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Splice Cassette, 24 LC, blue

OBSOLETE

This product was discontinued on: December 20, 2019

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Fiber cassette
Product Brand	MPOptimate®
Product Series	UCP

General Specifications

Application	For use with Universal Connectivity Product (UCP) panels
Adapter Color	Blue
Adapters, quantity, front	6
Body Style	Quad
Color, front	Black
Color, housing	Black
Interface, front	LC/UPC
Interface, rear	No pigtail
Total Fibers, quantity	24
Total Ports, quantity, front	24

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

1671965-3

Packaging and Weights

Packaging quantity 1
Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

